

Naziv PDF datoteke



VALENA LIFE LEGRAND

Rotary dimmer Valena Life - 240 V~ - 50 Hz - with cover plate - white

REF. 752160 | EAN KODA. 3414970465092

[> The product details page](#)

Značilnosti izdelka:

- Valena™ Life - dimmers with cover plate - Valena In'Matic mechanisms supplied with cover plates and support frames - To be equipped with plates - Supplied with mounted dust protection transparent shield - Flowpack packaging: robust protection to ensure optimum operation
- Dimmers 240 V~ - 50 Hz - Equipped with overvoltage and short-circuit protection - When switched on, lights up at the level set before last switch-off - Can be remotely controlled via non-illuminated push-buttons (Cat.No 7 520 11), with each push-button able to perform the ON/OFF and dimming function Rotary dimmer without neutral - For all types of lamps: - dimmable LEDs: 5 W to 75 W (10 lamps max.) - dimmable compact fluorescent lamps: 5 W to 75 W (10 lamps max.) - halogen with ferromagnetic or electronic transformer: 5 VA to 300 VA - fluorescent tube - ballast: 5 VA to 300 VA - halogen and incandescent 240 V~: 5 W to 300 W - When switched on, gradually (2 seconds) lights up at the level set before last switch-off - White

Dokumentacija

Tehnična dokumentacija



LE07432AC.pdf | PDF (0.7Mo)



LE07432AB_hermes.pdf | PDF (1.88Mo)



F01954FR-02.pdf | PDF (0.62Mo)



F01954EN-02.pdf | PDF (0.62Mo)