

Naziv PDF datoteke



DLP LEGRAND

Snap-on trunking 3 compartments white 50x180mm, length 2m

REF. 075606 | EAN KODA. 3245060756062

> [The product details page](#)

Značilnosti izdelka:

- Delivered with 3 covers, width 45mm
- Wiring capacity : maximum diameter 38mm
- Cross - section : compartment A and C 2442mm² and compartment B 1950mm²
- Compatible with all the functions of Mosaic Program
- IP40 : protected against solid bodies larger 1mm maximum

Prednosti montaže:

- Fixing by: wall plugs for immediate fixing (cat.no 030899), DLP rapid wall plug (ref 0308 97) or screw, nails...

Prednosti uporabe:

- Can be installed in tertiary and residential

Dokumentacija

Tehnična dokumentacija

-  LE01020AB.pdf | PDF (0.4Mo)
-  F00886FR-04.pdf | PDF (1.06Mo)
-  F00886EN-06.pdf | PDF (1Mo)

CAD & specifikacije načrtov / BIM

- BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt | RVT (23.93Mo)
- BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt | RVT (14.36Mo)
- BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt | RVT (13.17Mo)

Katalog & drugo

-  ex223001_1066-1067.pdf | PDF (0.17Mo)
-  ex223001_1061.pdf | PDF (0.13Mo)

Pogodbe in certifikati

-  LGRP-01604-V02.01-EN.pdf | PDF (0.74Mo)
-  LGRP-01604-V02.01-FR.pdf | PDF (0.71Mo)