

Naziv PDF datoteke



LEGRAND

Standard LED emergency luminaire Twinspot - non autotest - 2 x 450 lm - 1h

REF. 661451 | EAN KODA. 3414970575760

> [The product details page](#)

Značilnosti izdelka:

- LED Twinspot emergency lighting luminaires - High performance LED non maintained emergency lighting luminaires - Certified to IEC and EN 60598 - 2 - 22 standards - High power LEDs spotlights with optimized lighting distribution - Low consumption electronic switching power supply - High capacity terminals : 2 x 2.5 mm² - IP 55 - IK 07 - Duration : 1, 2 and 3 hours. Ni - Cd batteries. Recharge time : 24h - Green charge indicator with high luminosity LED, to improve visibility from the floor when high installation - Power supply : 230 V~ ± 10% - 50/60 Hz. Class II - Rest mode with remote control device Cat.No 0 039 01 to avoid battery discharge in case of voluntary power cut - Surface mounting installation with 4 wall - mounting lugs (Cat.No 0 358 02, supplied) or 4 screws (not supplied)
- Standard LED spotlight luminaires - non-Maintained (NM) - 2 x 450 lm 1h

Dokumentacija

Tehnična dokumentacija



LE08274AD.pdf | PDF (1.6Mo)

Katalog & drugo



ex223001_0912.pdf | PDF (0.07Mo)