

Naziv PDF datoteke



SYNERGY™ LEGRAND

Synergy™ - Single pole switch - 2 gang - 1 way - 10 AX
250 V~ - White

REF. 730024 | EAN KODA. 3245067300244

> [The product details page](#)

Značilnosti izdelka:

- Synergy - single pole switches, single pole push and key switches, rotary dimmers - white - Front plates : white thermoset - Terminal screws captive and backed off ready for cabling - large angled terminal entries - Compact mechanism for maximised wiring space - Supplied with faceplate screw caps
- Single pole plate switches 10 AX - 250 V~ - Conform to BS EN 60669 - 1 - For flush-mounting, back box to be min. 16 mm deep - ASTA licence Nominal plate dimensions : 86 x 86 mm - 2 gang - 1 way

Dokumentacija

Tehnična dokumentacija

 F00223EN-03.pdf | PDF (0.59Mo)

Pogodbe in certifikati

 LGRP-2015-309-V1-EN.pdf | PDF (0.62Mo)

 OC / CB-FR_708093 | (0.72Mo)

Katalog & drugo

 ex223001_0716.pdf | PDF (0.06Mo)