

# Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - Double RJ45 socket inclined 45° category 5e UTP 2 modules white

REF. 076502 | EAN KODA. 3245060765026

> [The product details page](#)

## Značilnosti izdelka:

- RJ45 Cat 5e : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 2 modules
- White

## Priporočila / omejitve

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

## Prednosti montaže:

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

## Prednosti uporabe:

- The 45° tilt angle prevents the cord and the socket from wear and tear. Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

## Edinstvene značilnosti:

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

## Dokumentacija

### Tehnična dokumentacija

-  F00948EN-05.pdf | PDF (1.93Mo)
-  F00948FR-05.pdf | PDF (1.94Mo)
-  LE01557AK.pdf | PDF (1.59Mo)
-  LE01557AJ.pdf | PDF (1.55Mo)

### Katalog & drugo

-  ex223001\_1189.pdf | PDF (0.11Mo)
-  ex223001\_0992.pdf | PDF (0.08Mo)

Pogodbe in certifikati

-  LGRP-00945-V02.01-FR.pdf | PDF (0.8Mo)
-  AoC-PL2\_C5e\_UTP\_32751\_ac1181027 (H | (0.07Mo)
-  AoC-SA01\_SB01\_ac109590 | (0.06Mo)
-  AoC-CL2\_C5e\_UTP\_32751\_ac1181028 | (0.07Mo)
-  LGRP-00945-V02.01-EN.pdf | PDF (0.8Mo)