

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - RJ45 socket category 6 FTP 2 modules white with orange shutter

REF. 076523 | EAN KODA. 3245060765231

> [The product details page](#)

Značilnosti izdelka:

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 1 module
- White with green shutter

Priporočila / omejitve

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

Prednosti montaže:

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Prednosti uporabe:

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Edinstvene značilnosti:

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Dokumentacija

Tehnična dokumentacija

- F00949FR-08.pdf | PDF (0.78Mo)
- LE01557AK.pdf | PDF (1.59Mo)
- LE01557AJ.pdf | PDF (1.55Mo)
- F00949EN-08.pdf | PDF (0.78Mo)

Pogodbe in certifikati

- LGRP-00945-V02.01-FR.pdf | PDF (0.8Mo)

Katalog & drugo

- ex223001_0986.pdf | PDF (0.11Mo)
- ex223001_1188.pdf | PDF (0.12Mo)

	LGRP-00945-V02.01-EN.pdf PDF (0.8Mo)
	AoC-Ac Delta Force 4PPoE 2019-677 (0.08Mo)
	AoC-PL2_Cat6FTP3275632856ac1181020 (0.07Mo)
	AoC-SA52_SB52_ac109588 (0.06Mo)
	AoC-CL2_Cat6FTP3275632856ac1181021 (0.07Mo)
	AoC-PL3_Cat6_FTP_32756_ac1181022 (0.07Mo)