

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - RJ45 socket category 6A UTP 1 module white with orange shutter

REF. 076527 | EAN KODA. 3245060765279

> [The product details page](#)

Značilnosti izdelka:

- RJ45 Cat 6A : Data rate up to 10 GigaBit/s. This allows you to download a 1 GigaBytes file in 1 second.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 1 module
- White with orange shutter

Priporočila / omejitve

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

Prednosti montaže:

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Prednosti uporabe:

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Edinstvene značilnosti:

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Dokumentacija

Tehnična dokumentacija

 F01436EN-02.pdf | PDF (2.27Mo)

Pogodbe in certifikati

 LGRP-00420-V01.01-EN.pdf | PDF (0.63Mo)

 LGRP-01330-V02.01-FR.pdf | PDF (0.81Mo)

 AoC-CL2_Cat6A_UTP_32787_ac1171013 | (0.08Mo)

Katalog & drugo

 ex223001_1188.pdf | PDF (0.12Mo)

 ex223001_0981.pdf | PDF (0.11Mo)



LGRP-01330-V02.01-EN.pdf | PDF (0.82Mo)



AoC-PL2_Cat6A_UTP_32787_ac1171012 | (0.08Mo)