

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - RJ45 socket with retractable cord 0.9m
category 6 FTP 4 modules white

REF. 076533 | EAN KODA. 3245060765330

> [The product details page](#)

Značilnosti izdelka:

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector, and a retractable integrated cord to plug easily your device.
- 4 modules
- White

Priporočila / omejitve

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

Prednosti montaže:

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

Prednosti uporabe:

- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

Edinstvene značilnosti:

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

Dokumentacija

Tehnična dokumentacija



S000082622FR-00.pdf | PDF (0.96Mo)



LE03018AB.pdf | PDF (1.76Mo)

Katalog & drugo



ex223001_1189.pdf | PDF (0.11Mo)



ex223001_0986.pdf | PDF (0.11Mo)