

# Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - RJ45 socket category 6 FTP 2 modules white  
REF. 076565 | EAN KODA. 3245060765651

> [The product details page](#)

## Značilnosti izdelka:

- RJ45 Cat 6 : Data rate up to 1 GigaBit/s. This allows you to download a 1 GigaBytes file in 8 seconds.
- Support high capacity PoE applications. Power over Ethernet pass electric power along with data on twisted pair Ethernet cabling.
- Equipped with a transparent protective dust cover protecting the connector.
- 2 modules
- White

## Priporočila / omejitve

- Conform to standards ISO/IEC 11801 Ed. 3.0, EN 50173-1 and TIA/EIA 568 C. Indoor use only.

## Prednosti montaže:

- Supplied with rocker plates, to be equipped with support frames and plates. Equipped with connectors with quick toolless connection.

## Prednosti uporabe:





- Suitable for commercial and residential installation. IP and analog phones. Very suitable for downloads, streaming or online games requiring low latency.

## Edinstvene značilnosti:

- Toolless connector with fast connection thanks to integrated crimping.
- Compatible with cords equipped with RJ11, RJ12 or RJ45 plugs.
- Slot system allows a perfect and easy multigang setting. The support frames can be perfectly joined thereby easing the installation. Can be installed in a normal (single) flush mounting box, no need to additional wall groove cutting or cabling.

## Dokumentacija



### Tehnična dokumentacija

-  LE01557AK.pdf | PDF (1.59Mo)
-  F00949FR-08.pdf | PDF (0.78Mo)
-  LE01557AJ.pdf | PDF (1.55Mo)
-  F00949EN-08.pdf | PDF (0.78Mo)

### CAD & specifikacije načrtov / BIM

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

### Katalog & drugo

-  ex223001\_1188.pdf | PDF (0.12Mo)
-  ex223001\_0986.pdf | PDF (0.11Mo)

### Pogodbe in certifikati

-  LGRP-00945-V02.01-EN.pdf | PDF (0.8Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

-  AoC-PL2\_Cat6FTP3275632856ac1181020 | (0.07Mo)
-  AoC-Ac Delta Force 4PPoE 2019-677 | (0.08Mo)
-  AoC-PL3\_Cat6\_FTP\_32756\_ac1181022 | (0.07Mo)
-  AoC-SA52\_SB52\_ac109588 | (0.06Mo)
-  AoC-CL2\_Cat6FTP3275632856ac1181021 | (0.07Mo)