

Naziv PDF datoteke



HYPRA LEGRAND

Panel mounting socket Hypra - IP 44 - 20/25 V~ - 32 A - 2P - plastic

REF. 052501 | EAN KODA. 3245060525019

> [The product details page](#)

Značilnosti izdelka:

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prisinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prisinter) ELV panel mounting sockets 20 to 25 V~ - 50/60 Hz - 32 A 2P - To be associated with surface - mounting box Cat.No 0 524 19 for surface - mounting socket - Plastic - 32 A

Dokumentacija

Tehnična dokumentacija

-  F00138FR-04.pdf | PDF (1.44Mo)
-  F00138EN-04.pdf | PDF (1.25Mo)

CAD & specifikacije načrtov / BIM

- LEGRAND_PRISES_NON_VERROUILLEES_ENCASTREES_IP44_20.rfa | RFA (0.86Mo)
-  052401.dwg | DWG (0.13Mo)
- LEGRAND_NON_INTERLOCKED_SOCKETS_SURFACE_MOUNTED_IP44_20_SYMBOL.rfa | RFA (0.33Mo)
- LEGRAND_NON_INTERLOCKED_SOCKETS_SURFACE_MOUNTED_IP44_20.rfa | RFA (0.6Mo)
- LEGRAND_NON_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_IP44_20.rfa | RFA (0.86Mo)
- LEGRAND_PRISES_NON_VERROUILLEES_SAILLIES_IP44_20_SYMBOL.rfa | RFA (0.33Mo)
- LEGRAND_NON_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_IP44_20_SYMBOL.rfa | RFA (0.33Mo)
- LEGRAND_PRISES_NON_VERROUILLEES_SAILLIES_IP44_20.rfa | RFA (0.6Mo)
- LEGRAND_PRISES_NON_VERROUILLEES_ENCASTREES_IP44_20_SYMBOL.rfa | RFA (0.33Mo)

Pogodbe in certifikati

-  OC / CB-FR_710634 | (0.7Mo)

