

Naziv PDF datoteke



HYPRA LEGRAND

Mobile socket Hypra - IP44 - 380/415 V~ - 32 A - 3P+N+E - plastic

REF. 052984 | EAN KODA. 3245060529840

> [The product details page](#)

Značilnosti izdelka:

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prinsinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prinsinter) LV mobile sockets 380 to 415 V~ 50/60 Hz - 32 A 3P+N+E - Plastic - 32 A

Dokumentacija

Tehnična dokumentacija

 F00138FR-04.pdf | PDF (1.44Mo)

 F00138EN-04.pdf | PDF (1.25Mo)

Pogodbe in certifikati

 LGRP-2015-017-V1-EN.pdf | PDF (0.62Mo)

 OC / CB-FR_710634 | (0.7Mo)

CAD & specifikacije načrtov / BIM

 052984.dwg | DWG (0.09Mo)