

# Naziv PDF datoteke



LEGRAND

Line tap - non-shear - with feet - capacity per tap 2x16 mm<sup>2</sup> - hexagonal head

REF. 034042 | EAN KODA. 3245060340421

> [The product details page](#)

## Značilnosti izdelka:

- Line taps and equipotential bonding connectorsLine tapsNon-shear line taps- Hexagonal head - With feet - Capacity per tap : 2 x 16 mm<sup>2</sup>- Width of slot : 5.8 max. cable Ø in mm- Overall height : 41 mm- Fixing centres : 37 mm

## Dokumentacija

### Tehnična dokumentacija

-  F00003-01fr.pdf | PDF (0.04Mo)
-  F00003-01en.pdf | PDF (0.04Mo)
-  0064U92-01.pdf | PDF (0.01Mo)

### Katalog & drugo

-  ex223001\_0820.pdf | PDF (0.22Mo)