

Naziv PDF datoteke



HYPRA LEGRAND

Panel mounting socket Prisinter Hypra -IP 44/55 - 200/250V~ -16 A - 2P+E - metal

REF. 052012 | EAN KODA. 3245060520120

> [The product details page](#)

Značilnosti izdelka:

- Hypra IP 44 sockets and plugs metal, plastic, rubber, IP 44/55 Prisinter - LV 16 to 63 A and ELV 16 and 32 A - Conform to IEC 60309 - 1 and IEC 60309 - 2 - IP 44 according to IEC 60529 - IK 09 : plastic and rubber - IK 10 : metal according to IEC 62262 - Self - extinguishing : - 850°C (support of active parts) / 960 °C for Prinsinter) - 650 °C : plastic housing conform to IEC 60695 - 2 - 10 - 50°C to + 100°C (- 20°C for Prisinter) LV prisinters - Dust resistance IP may be increased by rubber push - button (on request) - IP 55 cover closed or connected - IP 44 connected 200 to 250 V~ 50/60 Hz - 16 A 2P+E - To be associated with surface - mounting box Cat. No 0 520 49 for surface - mounting socket - Panel mounting socket - metal - 16 A

Dokumentacija

Tehnična dokumentacija

-  F00097FR-05.pdf | PDF (0.88Mo)
-  F00097EN-05.pdf | PDF (0.99Mo)

Pogodbe in certifikati

-  OC / CB-FR_710635/A1 | (0.72Mo)

CAD & specifikacije načrtov / BIM

-  052002.dwg | DWG (0.17Mo)
- LEGRAND_PRISES_VERROUILLEES_ENCASTREES_230.rfa | RFA (0.59Mo)
- LEGRAND_INTERLOCKED_SOCKETS_FLUSH_MOUNTED_230.rfa | RFA (0.58Mo)