

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - Proximity MCB - single pole - with neutral
230 V~ - 10 A - 2 mod - white

REF. 077521 | EAN KODA. 3245060775216

> [The product details page](#)

Značilnosti izdelka:

- Mosaic™ Programme mechanisms - voltage surge protector, replacement module, filter, buzzers, bells, blanking plates, cable outlets and proximity MCBs
- Proximity MCBs - Used for local protection of part of a circuit against overloads and short circuits - Used in addition to the main protection device - Due to its proximity to the user and its discrimination with the main protection device, the restart can be immediate - 2 modules Single pole thermal magnetic MCB + Neutral 230 V~ - Can also be used as a local consumption limiter (depending on its rating) - Breaking capacity : 3000 A - NF C 61 - 410 (10/16 A) 1500 A - NF C 61 - 410 (6 A) - White - 10A

Dokumentacija

Katalog & drugo

 ex223001_1187.pdf | PDF (0.21Mo)

Pogodbe in certifikati

 OC / CB-8320-M1 | (0.08Mo)

 IMQ-CA03.00605 | (0.25Mo)

CAD & specifikacije načrtov / BIM

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)