


Naziv PDF datoteke



LCS³ LEGRAND

Patch panel 19 inch - equipped with 24 RJ45 Category 6A STP

REF. 033772 | EAN KODA. 3414970870704

This 19 inch patch panel is ready to use with 24 RJ45 and also a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

> [The product details page](#)

Splošni opis:

This 19 inch patch panel is ready to use with 24 RJ45 and also a new generation quick-fix mechanism for automatic screwless mounting on the cabinets uprights. The automatic removal of each cassette is possible using a push button.

Značilnosti izdelka:

- Equipped with 4 extractable cassettes each containing 6 connectors. Cat 6A STP RJ45 quick - connect connectors (no tools required), with 568 A/B marking.
- Equipped with rear cable guide to hold the cables.
- 19" panel - 1 U.
- Supplied with coloured labels, white yellow, blue and red.
- The panel ensure automatic earthing of each connector.

Priporočila / omejitve

- Compliant with ISO/IEC 11801 edition 3.0 (2017) and EIA/TIA 568 C2-1 standards

Prednosti montaže:

- Front-panel and fast-snap accessibility of each individual connector provide ease and reliability for installation and maintenance. Universal and secured mounting on any cabinet or enclosure through new generation quick-fix anchorage. Automatic cassette removal by a simple button press. Hands-free cassette support during installation or maintenance while in the extracted position.

Prednosti uporabe:

- Daily user maintenance is rendered easy through the move-add-change management of each cassette and individual connector.

Edinstvene značilnosti:

- Save time at both installation and in daily maintenance by taking advantage of the screwless mounting and the automatic removal of each cassette.

Dokumentacija

Tehnična dokumentacija

- LE09727AD.pdf | PDF (4.73Mo)
- S000096850FR-06.pdf | PDF (8.19Mo)
- S000096850EN-06.pdf | PDF (8.19Mo)

CAD & specifikacije načrtov / BIM

- Flat patch panels equipped copper.rfa | RFA (0.94Mo)
- Panneaux de brassages droits équipés cuivre.rfa | RFA (0.85Mo)

Katalog & drugo

- ex223001_0978.pdf | PDF (0.16Mo)

Pogodbe in certifikati

- AoC-CL2_Cat6A_FTP_32778_ac1171015 | (0.08Mo)
- AoC-PL2_C6A_UFTP_32884_ac1191058 | (0.06Mo)

	AoC-PL2_Cat6A_FFTP_32799_ac1171009 (0.07Mo)
	AoC-4PPoE 2019-676 Ac Delta Force (0.08Mo)
	AoC-PL2_Cat6A_STP_32777_ac1171017A (0.08Mo)
	AoC-CL2_C6A_UFTP_32884_ac1191059 (0.06Mo)
	LGRP-00626-V02.01-EN.pdf PDF (0.95Mo)
	AoC-PL3_Cat6A_STP_32777_ac1171019A (0.08Mo)
	AoC-CL4_Cat6A_STP_32869_ac1181045 (0.08Mo)
	AoC-PL2_Cat6A_FTP_32778_ac1171014 (0.08Mo)
	LGRP-00626-V02.01-FR.pdf PDF (0.96Mo)
	AoC-CL2_Cat6A_STP_32777_ac1171018A (0.08Mo)
	AoC-CL2_Cat6A_FFTP_32799_ac1171010 (0.07Mo)
	AoC-PL3_Cat6A_FTP_32778_ac1171016 (0.08Mo)
	AoC-CL2_C6A_STP_32882_ac1191063 (0.06Mo)
	AoC-CL4_Cat6A_STP_32778_ac1181044 (0.08Mo)
	AoC-Composant Cat6A STP 3P-1200331 (0.06Mo)
	AoC-CL2_C6A_FFTP_32883_ac1191061 (0.06Mo)
	AoC-PL2_C6A_FFTP_32883_ac1191060 (0.06Mo)
	AoC-PL2_C6A_STP_32882_ac1191062 (0.06Mo)
	AoC-PL3_Cat6A_FFTP_32799_ac1171011 (0.07Mo)