

Naziv PDF datoteke



LEGRAND

Flexible conduit - high impact - shock resistance 6 joules - Ø ext. 32 mm

REF. 651232 | EAN KODA. 3245066512327

[> The product details page](#)

Značilnosti izdelka:

- Flexible conduits - Non flame propagating - Conform to standard EN/IEC 61386 - 22 - Crush resistance : 750 Newtons - Supplied wrapped in film, the coil acts as a pay - out reel - The various diameters are identified by coloured ties - Surface - mounting or flush-mounting High impact with draw wire (ICTA 3422) - Polyolefin additives - Dark grey (RAL 7024) - Impact resistance : 6 joules at - 5 °C - Min operating t° : - 5 °C - Max operating t° : + 90 °C - IK 08 - Prelubricated inner surface for easy pulling of the wires - Nylon - coated steel wire puller for a better resistance to corrosion - Surface mounting not recommended outside - Suitable for prefabricated concrete - colour of ties on coil : white - Ø exterior : 32 mm - Ø interior : 24.3 mm - thickness : 3.85 mm

Dokumentacija

Tehnična dokumentacija

 F00924EN-00.pdf | PDF (0.12Mo)

Pogodbe in certifikati

 LGRP-01020-V02.01-FR.pdf | PDF (0.7Mo)

Katalog & drugo

 ex223001_0809.pdf | PDF (0.25Mo)