

Naziv PDF datoteke



LEGRAND

Flexible conduit - medium impact - shock resistance 2 joules - Ø ext. 40 mm

REF. 651040 | EAN KODA. 3245066510408

> [The product details page](#)

Značilnosti izdelka:

- Flexible conduits - Non flame propagating - Conform to standard EN/IEC 61386 - 22 - Crush resistance : 750 Newtons - Supplied wrapped in film, the coil acts as a pay - out reel - The various diameters are identified by coloured ties - Surface - mounting or flush-mounting Medium impact (ICA 3321) - PVC without Pb, Sn, Cd (RoHS compliant) - Light grey (RAL 7035) - Impact resistance : 2 joules at - 5 °C - Min operating t° : - 5 °C - Max operating t° : + 60 °C - IK 07 - Flush - mounted in certain cases before construction of the masonry - colour of ties on coil : white - Ø exterior : 40 mm - Ø interior : 31.2 mm - thickness : 4.40 mm

Dokumentacija

Katalog & drugo



ex223001_0809.pdf | PDF (0.25Mo)