

Naziv PDF datoteke



DLPLUS LEGRAND

Variable external angle for DLPlus mini-trunking
60x20mm

REF. 030292 | EAN KODA. 3245060302924

> [The product details page](#)

Značilnosti izdelka:

- Variable external angle of 60 to 120 degrees
- Respect the protection index
- Improvement of aesthetics (covering of the cut)
- Colour: white

Prednosti montaže:

- Clipper directly on the body of the mini-trunking

Prednosti uporabe:

- Allows a neat and clean electrical installation finish

Dokumentacija

Tehnična dokumentacija

 F00988EN-06.pdf | PDF (2.71Mo)

 F00988FR-04.pdf | PDF (2.59Mo)

Pogodbe in certifikati

 LGRP-01603-V02.01-EN.pdf | PDF (0.92Mo)

 LGRP-01603-V02.01-FR.pdf | PDF (0.88Mo)

Katalog & drugo

 ex223001_1046.pdf | PDF (0.12Mo)

 ex223001_1048.pdf | PDF (0.04Mo)