

Naziv PDF datoteke



DLP LEGRAND

Variable external angle for snap-on trunking
50x130mm

REF. 075633 | EAN KODA. 3245060756338

> [The product details page](#)

Značilnosti izdelka:

- Variable external angle of 85 to 120 degrees
- Respect the protection index
- Improvement of aesthetics (covering of the cut)
- Composed with 2 elements for trunking 1 compartment, or 3 elements for trunking 2 compartments with partition junction
- Colour: white

Prednosti montaže:

- Clipper directly on the body of the trunking

Prednosti uporabe:

- The external angles ensure the continuity of the flexible cover on the angles, hence preventing cut of cover and being aesthetic

Dokumentacija

Tehnična dokumentacija

 F00886FR-04.pdf | PDF (1.06Mo)

 F00886EN-06.pdf | PDF (1Mo)

 LE01001AB.pdf | PDF (0.41Mo)

CAD & specifikacije načrtov / BIM

BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt | RVT (14.36Mo)

BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt | RVT (13.17Mo)

BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt | RVT (23.93Mo)

Katalog & drugo

 ex223001_1066-1067.pdf | PDF (0.17Mo)

 ex223001_1060.pdf | PDF (0.14Mo)

Pogodbe in certifikati

 LGRP-01604-V02.01-EN.pdf | PDF (0.74Mo)

 LGRP-01604-V02.01-FR.pdf | PDF (0.71Mo)