

Naziv PDF datoteke



LEGRAND

Plinth - for Marina enclosures - height 170 mm

REF. 036296 | EAN KODA. 3245060362966

> [The product details page](#)

Značilnosti izdelka:

- Marina enclosures - polyester - IP 66 - IK 10 - IP 66 acc. to IEC EN 60529. LCIE n° 60059283 - 560528 - IK 10 acc. to EN 62262 (EN 50102) - Class II (Used to create totally isolated assemblies acc. to EN 60439 - 1) - Fiberglass reinforced polyester. Self - extinguishing 960°C acc. to IEC EN 60695 - 2 - 11 - Adapted to corrosive environment. Supplied with Fixing kit for plain plates or sectionned uprights - Depth adjustment of equipment - Equipped with low cable entries plate - Reversible door with strand - holder - 3 point closing with handle fitted with 1/2 locking latch 2433 A (other key code, please consult us) - Stainless steel hinges and hinges axis
- Plinth RAL 7035 - Height 170 mm - Front and rear trap door - Possibility to overlap 2 plinths - For enclosure width 800 x depth 400 mm

Dokumentacija

Katalog & drugo

-  ex223001_0424.pdf | PDF (0.12Mo)
-  ex223001_0426-0427.pdf | PDF (0.36Mo)
-  ex223001_0428.pdf | PDF (0.39Mo)

CAD & specifikacije načrtov / BIM

-  036296.dwg | DWG (0.04Mo)