

Naziv PDF datoteke



LEGRAND

Plinth for Atlantic E cabinet - 600x300 - RAL 7016

REF. 036300 | EAN KODA. 3245060363000

> [The product details page](#)

Značilnosti izdelka:

- Atlantic metal cabinets supplied with plain plate - IP 55/IP 66 - IK 10 - Type 4x - Type 12 - IP 66 according to standards IEC EN 60529 for 1-door cabinets - IP 55 according to standards IEC EN 60529 for 2-door cabinets - IK 10 according to standards IEC EN 62262 - LCIE 17 07 90 10A - Type 4x, 1 door, Type 12, 2 doors - cULus, Bureau Veritas - EMC attenuation 20 dB (for an EMC attenuation from 40 to 50 dB at 1 GHz, please consult us) - Excellent resistance to corrosion and chemical agents - 80 µm thick textured polyester coating. Anti-corrosion treatment for hinges and pins - Reversible door - Fitted with lever - Supplied with double bar lock - Self-centering positioning system for the equipment - Compatible with all Atlantic accessories Low cable entries RAL 7035 - Optional depth adjustment for cabinets 400 mm depth, with slide rails Cat.No 0 367 45
- Plinths RAL 7016 - Height 200 mm - Front and rear trap door - For cabinets Width : 600 mm - For cabinets Depth : 300 mm - Weight : 6 kg

Dokumentacija

Tehnična dokumentacija

 041401-01.pdf | PDF (0.32Mo)

CAD & specifikacije načrtov / BIM

 036300.dwg | DWG (0.04Mo)

Katalog & drugo

 ex223001_0420-0421.pdf | PDF (0.28Mo)

 ex223001_0416.pdf | PDF (0.06Mo)