

Naziv PDF datoteke



LEGRAND

Cable glands metal - IP 68 - ISO 16 - Clamping capacity diameter 4-9.5 mm

REF. 095501 | EAN KODA. 3245060955014

[> The product details page](#)

Značilnosti izdelka:

- Metal cable glands IP 68 - ISO and PG
- Metal cable glands - Mechanically tightened cable glands with neoprene weatherproof seal for IP 68 protection. - Locking part consisting of flexible blades which exert strong pressure on the cable thus giving the product excellent tensile strength - Supplied with surface seal mounted ISO - Conform to EN 50262 - ISO : 16 - Clamping capacity Min. : 5.5 mm - Clamping capacity Max. : 9.5 mm

Dokumentacija

Tehnična dokumentacija



F02550FR00.pdf | PDF (2.13Mo)

CAD & specifikacije načrtov / BIM



095501.dwg | DWG (0.1Mo)

Katalog & drugo



ex223001_0445.pdf | PDF (0.06Mo)

Pogodbe in certifikati



LGRP-2014-115-V1-EN.pdf | PDF (0.96Mo)