

Naziv PDF datoteke



LEGRAND

MCCB - DRX 125 - thermal magnetic - Icu 10 kA - 415 V~ - 4P - In 60 A

REF. 027016 | EAN KODA. 3245060270162

> [The product details page](#)

Značilnosti izdelka:

- DRX 125 - thermal magnetic MCCBs from 15 to 125 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : - M5 terminal for In ≤ 50 A and M8 range for In 50 A - Fixing screws - Insulating shields (2 for 3P and 3 for 4P) - Fixed thermal and magnetic - Conform to IEC 60947 - 2, in compliance with NEMA
- DRX 125 Breaking capacity Icu 10 kA (415 V~) - 4P - 60 A

Dokumentacija

Tehnična dokumentacija

-  F00699EN06_DRX125.pdf | PDF (0.96Mo)
-  Y1036G.pdf | PDF (0.58Mo)

CAD & specifikacije načrtov / BIM

-  027010.dwg | DWG (0.23Mo)

Katalog & drugo

-  ex223001_0132.pdf | PDF (0.13Mo)
-  ex223001_0136.pdf | PDF (0.07Mo)
-  ex223001_0138.pdf | PDF (0.05Mo)

Pogodbe in certifikati

-  OC / CB-SE 57100 | (0.2Mo)
-  LGRP-01099-V01.01-EN.pdf | PDF (0.62Mo)
-  OC / CB-SE-101774A1 | (0.42Mo)