

Naziv PDF datoteke



LEGRAND

MCCB - DRX 125 - thermal magnetic - Icu 20 kA - 415 V~ - 3P - In 15 A

REF. 027020 | EAN KODA. 3245060270209

> [The product details page](#)

Značilnosti izdelka:

- DRX 125 - thermal magnetic MCCBs from 15 to 125 A - For switching, control, isolation and protection of low - voltage electrical lines - Can be fitted with auxiliaries - Supplied with : - M5 terminal for In ≤ 50 A and M8 range for In 50 A - Fixing screws - Insulating shields (2 for 3P and 3 for 4P) - Fixed thermal and magnetic - Conform to IEC 60947 - 2, in compliance with NEMA
- DRX 125 Breaking capacity Icu 20 kA (415 V~) - 3P - 15 A

Dokumentacija

Tehnična dokumentacija

 F00699EN06_DRX125.pdf | PDF (0.96Mo)

 Y1036G.pdf | PDF (0.58Mo)

CAD & specifikacije načrtov / BIM

 027068.dwg | DWG (0.19Mo)

Katalog & drugo

 ex223001_0132.pdf | PDF (0.13Mo)

 ex223001_0136.pdf | PDF (0.07Mo)

 ex223001_0138.pdf | PDF (0.05Mo)

Pogodbe in certifikati

 LGRP-01099-V01.01-EN.pdf | PDF (0.62Mo)

 LOVAG-06.001/003/005 | (0.34Mo)

 OC / CB-SE-101774A1 | (0.42Mo)

 OC / CB-SE 57102 | (0.2Mo)