

Naziv PDF datoteke



LEGRAND

On-line double conversion UPS - with isolation transformer - 6000 VA - 5400 W

REF. 310129 | EAN KODA. 3245063101296

> [The product details page](#)

Značilnosti izdelka:

- Keor S - On - line double conversion UPS (tower) - single phase - For industrial environment (food industry, laboratories ...) or applications requiring long backup time (electro - medical ...) - Installation : downstream power generators. Possibility to add batteries for extended autonomy. Parallel connection possible : up to 4 UPSs. Advanced management depending on the battery discharge level - Sinusoidal output - LCD screen - Self - diagnosis - Power factor : 0,9 - Integrated automatic bypass and maintenance bypass. Integrated slot for installing a communication interface for Ethernet network connection, to be ordered separately - Cold Start Function. Microprocessor control - Telephone line/Internet (RJ 11/ RJ45) - Remote emergency shutdown function ("Emergency Power Off" - EPO). Equipped with 4 wheels for easy moving of the UPS
- UPS with isolation transformer - The stated backup time in minutes is estimated and may vary according to the load characteristics, operating conditions and environment - Nominal power : 6000 VA - Active power : 5400 W - Backup time : 0 min - Weight : 100 kg

Dokumentacija

Tehnična dokumentacija

 UPS_LGR_0088_FR_AA.pdf | PDF (0.22Mo)

 EXB21082_EN.pdf | PDF (11.02Mo)

 UPS_LGR_0088_GB_AA.pdf | PDF (0.19Mo)

Katalog & drugo

 ex223001_0932.pdf | PDF (0.09Mo)