

Naziv PDF datoteke



LEGRAND

Time-lag switch - multifunction - 16 A - 230 V~ - 50/60 Hz - Lexic

REF. 004704 | EAN KODA. 4010957047047

> [The product details page](#)

Značilnosti izdelka:

- Electronic time - lag switches - Designed for supply busbar compatibility - Power supply : 230 V~ - 50/60 Hz - Switches a lighting circuit for a specific time - Self - protection in the event of blocked pushbutton
- Multi-function time - lag switch - Resettable - 230 V~ - 50/60 Hz - Timing adjustable from 0,5 sec to 12 min - Operation with 3 or 4 wires automatically recognised by the time - lag switch - Inputs for separate control 8 - 230 V (presence detection, lighting control by door entry system etc.) - Switch - off pre - warning function, - Long duration function (1 hour) and manual switch - off - Output 16 A - 250 V~ - $\cos \varphi = 1$ - 3680 W incandescent/halogen - 2000 W halogen 230 V~ - 1000 VA fluo - parallel compensated - 2000 VA compact fluorescent - 500 W halogen lamp + ferromagnetic transformer - 2000 W halogen lamp + electronic transformer - Specially suited to energy saving lamps 1000 W - Number of modules : 1

Dokumentacija

Tehnična dokumentacija



291959-08.pdf | PDF (1Mo)

CAD & specifikacije načrtov / BIM



004704.dwg | DWG (0.09Mo)

Katalog & drugo



ex223001_0106.pdf | PDF (0.09Mo)

Pogodbe in certifikati



VDE-40013008 | (0.28Mo)