

Naziv PDF datoteke



LEGRAND

Flush-mounting cabinet Nedbox - transparent door - 2 rows - 24+4 modules

REF. 001452 | EAN KODA. 3245060014520

> [The product details page](#)

Značilnosti izdelka:

- Flush-mounting cabinets Nedbox - 12 to 48 modules - IP 40 - IK 07 - Class II - Allows to achieve assemblies conform to IEC 61439 - 3 - Self extinguishing : resistance to incandescent wire 850°C
- Flush-mounting distribution cabinets - White RAL 9003 - Supplied with : - reversible door - screw terminal blocks for neutral and earth - Spacing between rails 125 mm - For installation in dry partitions use the flush-mounting kit Cat.No 0 014 90 With transparent door - Number of rows : 2 - Number of modules : 24 + 4 - Height : 430 mm - Width : 330 mm - Depth : 87 mm

Dokumentacija

Tehnična dokumentacija

 LE04724AA.pdf | PDF (0.97Mo)

 F02428EN_03.pdf | PDF (0.57Mo)

 F02428FR_03.pdf | PDF (0.58Mo)

CAD & specifikacije načrtov / BIM

 Legrand_Coffrets_modulaires_encastrés_Nedbox.rfa | RFA (2.47Mo)

 Legrand_Flush-mounting_cabinets_Nedbox.rfa | RFA (2.46Mo)

Katalog & drugo

 ex223001_0311.pdf | PDF (0.13Mo)

Pogodbe in certifikati

 LGRP-00856-V01.01-EN.pdf | PDF (0.6Mo)

 LOVAG-IT 16.040 | (1.35Mo)