

Naziv PDF datoteke



LEGRAND

Cabinets PLEXO³ - IP65 - IK09 - 3 rows - 18 modules

REF. 601837 | EAN KODA. 3245066018379

> [The product details page](#)

Značilnosti izdelka:

- Plexo³ - IP 65 weatherproof cabinets, multifunction sleeves and Accessories - Self - extinguishing : resistance to incandescent wire 650°C. - Allows to achieve assemblies conform to IEC 61 439 - 3 - Weatherproof cabinets - IP 65 - IK 09 - Class II - Door and cabinet fully reversible. Removable chassis and faceplates from 2 - row versions up - 2 - position rail for modular products and moulded cases. Spacing between rails 150 mm - Can be fitted with perforated plates and solid faceplates for mounting non-modular products - Lockable door handle, sealable cover and faceplate - Shock - resistant polystyrene material - Box colour light grey L750A, cover colour dark grey R746A - Supplied without terminal blocks
- Cabinets 18 modules per row - Number of rows : 3

Dokumentacija

Tehnična dokumentacija

-  F01043FR-03.pdf | PDF (1.2Mo)
-  EXB22009_Flipbook_FR_(03_2022).pdf | PDF (6.2Mo)
-  EXB22026_CA_Plexo3_FR_imprimable.pdf | PDF (33.87Mo)
-  F01043EN-05.pdf | PDF (1.07Mo)
-  EXB14046_CA_Plexo3_EN_print.pdf | PDF (34.53Mo)
-  EXB22010_Flipbook_EN_(03_2022).pdf | PDF (6.56Mo)

CAD & specifikacije načrtov / BIM

- Legrand_Cabinet_Plexo³_18_modules.rfa | RFA (8.2Mo)
- Legrand_Coffret_Plexo³_18_modules.rfa | RFA (8.2Mo)

Katalog & drugo

-  ex223001_0413.pdf | PDF (0.04Mo)
-  ex223001_0412.pdf | PDF (0.11Mo)

Pogodbe in certifikati

-  LOVAG-IT 17 .013-R02 | (1.1Mo)
-  OC / CB-654748 | (0.36Mo)
-  LGRP-00849-V01.01-EN.pdf | PDF (0.73Mo)