

Naziv PDF datoteke



LEGRAND

Proximity switching isolating switch - 3P + N/O + N/C - 20 A

REF. 022179 | EAN KODA. 3245060221799

> [The product details page](#)

Značilnosti izdelka:

- Proximity switching from 16 to 80 A - Safety switch for disconnection and isolation of phases - IP 2X - Double breaking on each phase - Red rotary handle on yellow plate - Immediate display of position - horizontal : open (O) - vertical : closed (I) - Equipped with non reversible terminals - Conform to IEC EN 60947 - 3 - UL - cUL (USA and Canada) agreements (except boxes) - IP 65 - IK 07 for boxes
- Proximity switching - Can be equipped with auxiliary contact Cat.No 0 227 00 - Padlockable boxes for on - load breaking, isolation and locking In = position - Equipment located remotely from a control cabinet - Applications : breaking of CMV (controlled mechanical ventilation) , motors, fixed or moving machines, air - conditioners 3P + N/O + N/C - yellow box - 20 A

Dokumentacija

Tehnična dokumentacija

 F00262FR-02.pdf | PDF (0.38Mo)

 096891000-01.pdf | PDF (0.3Mo)

CAD & specifikacije načrtov / BIM

 022179.dwg | DWG (0.1Mo)

Katalog & drugo

 ex223001_0255.pdf | PDF (0.08Mo)

 ex223001_0258.pdf | PDF (0.04Mo)

 ex223001_0257.pdf | PDF (0.04Mo)

Pogodbe in certifikati

 UL listed cULus-NLRV-E57817 | (0.07Mo)

 UL listed cUL-NLRV7-E57817 | (0.07Mo)