

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - PIR high density 360° lighting sensor Ø8m - IP42 - ceiling mounting

REF. 048804 | EAN KODA. 3245060488048

> [The product details page](#)

Značilnosti izdelka:

- PIR high density detection 360°, range Ø8m at 2,5m high
- IP42
- Switching control (3 - wire with neutral)
- Standby consumption: 0.8 W
- With an additional 2 A contact for HVAC control, based on presence data

Priporočila / omejitve

- Optimum distance between 2 sensors: 6 m

Prednosti montaže:

- Precise on-site adjustment using configuration tool Cat.No 0 882 40

Prednosti uporabe:

- Ideal for offices and working areas with natural light needing HVAC control

Edinstvene značilnosti:

- Can be used with push-button Cat.No 0 770 40 for vacancy mode (manual switch-on and manual or automatic switch-off)
- PIR high density uses a special lens designed to detect the slightest move
- Fix directly to a false ceiling with mounting claws (included) or installed in a Batibox box, depth 50 mm, Cat.No 0 893 58 Can be surface-mounted in ceiling using accessory Cat.No 0 488 75

Dokumentacija

Tehnična dokumentacija

-  LE07602AA.pdf | PDF (9.21Mo)
-  LE04870AC.pdf | PDF (1.24Mo)
-  S000074405FR_3.pdf | PDF (3.36Mo)
-  S000074405EN_3.pdf | PDF (3.36Mo)

CAD & specifikacije načrtov / BIM

Legrand_Gestion_eclairage_Detecteur_Presence_Plafond_autonome.rfa | RFA (3.23Mo)

Katalog & drugo

-  ex223001_0891.pdf | PDF (0.05Mo)
-  ex223001_0889.pdf | PDF (0.06Mo)

Pogodbe in certifikati

-  LGRP-01573-V01.01-EN.pdf | PDF (0.63Mo)
-  OC / CB-681064A | (1.18Mo)

Legrand_Lighting_Management_Standalone_Presence_Sensor_Ceilin
g.rfa | RFA (3.23Mo)