

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - Dual tech PIR + US 360° lighting sensor
Ø8m - IP20 - ceiling mounting

REF. 048806 | EAN KODA. 3245060488062

> [The product details page](#)

Značilnosti izdelka:

- PIR + US detection 360°, range Ø8m at 2,5m high
- IP20
- Switching control (3 - wire with neutral)
- Standby consumption: 0.8 W
- Connection via automatic terminals

Priporočila / omejitve

- Optimum distance between 2 sensors: 6 m

Prednosti montaže:

- Precise on-site adjustment using configuration tool Cat.No 0 882 40 Fixes directly to a false ceiling with mounting claws (included) or installed in a Batibox box, depth 50 mm Can be surface-mounted in ceiling using accessory Cat.No 0 488 75

Prednosti uporabe:

- Ideal for offices and working areas with natural light

Edinstvene značilnosti:

- Can be used with push-button Cat.No 0 770 40 for vacancy mode (manual switch-on and manual or automatic switch-off)
- Dual technology PIR and US ensures max sensitivity and coverage in tough application for optimum reliability

Dokumentacija

Tehnična dokumentacija

-  LE02605AG.pdf | PDF (1.52Mo)
-  S000073480EN_2.pdf | PDF (0.79Mo)
-  S000073480FR_2.pdf | PDF (0.79Mo)
-  LE07602AA.pdf | PDF (9.21Mo)

CAD & specifikacije načrtov / BIM

Legrand_Lighting_Management_Standalone_Presence_Sensor_Ceilin
g.rfa | RFA (3.23Mo)

Legrand_Gestion_eclairage_Detecteur_Presence_Plafond_autonome.r

Katalog & drugo

-  ex223001_0891.pdf | PDF (0.05Mo)
-  ex223001_1213.pdf | PDF (0.07Mo)
-  ex223001_0889.pdf | PDF (0.06Mo)

Pogodbe in certifikati

-  LGRP-00303-V02.01-EN.pdf | PDF (0.64Mo)
-  OC / CB-681064A | (1.18Mo)
-  LGRP-00303-V02.01-FR.pdf | PDF (0.64Mo)

fa | RFA (3.23Mo)