

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - PIR 360° lighting sensor 2x12m - IP41 - ceiling mounting

REF. 048817 | EAN KODA. 3245060488178

> [The product details page](#)

Značilnosti izdelka:

- PIR lateral detection 24 m - range 2 x 12 m
- IP41
- Switching control (3 - wire with neutral)
- Standby consumption: 0.4 W
- Connection via automatic terminals

Priporočila / omejitve

- Optimum distance between 2 sensors: 20 m

Prednosti montaže:

- Precise on-site adjustment using configuration tool Cat.No 0 882 40 Fix directly to a false ceiling with mounting claws (included) or installed in a Batibox box, depth 50 mm, Cat.No 0 893 58 Surface mounted on ceiling using accessory Cat.No 0 488 75

Prednosti uporabe:

- Ideal for passage areas with natural light

Edinstvene značilnosti:

- Can be used with push-button Cat.No 0 770 40 for vacancy mode (manual switch-on and manual or automatic switch-off)
- Fix directly to a false ceiling with mounting claws (included) or installed in a Batibox box, depth 50 mm, Cat.No 0 893 58 Can be surface-mounted in ceiling using accessory Cat.No 0 488 75

Dokumentacija

Tehnična dokumentacija

- LE07602AA.pdf | PDF (9.21Mo)
- S000072383FR_4.pdf | PDF (3.28Mo)
- LE04871AB.pdf | PDF (1.51Mo)
- S000072383EN_3.pdf | PDF (3.3Mo)

CAD & specifikacije načrtov / BIM

Legrand_Gestion_eclairage_Detecteur_Presence_Plafond_autonome.rfa | RFA (3.23Mo)

Katalog & drugo

- ex223001_0891.pdf | PDF (0.05Mo)
- ex223001_0888.pdf | PDF (0.07Mo)

Pogodbe in certifikati

- OC / CB-681064A | (1.18Mo)
- LGRP-00389-V02.01-EN.pdf | PDF (0.63Mo)

Legrand_Lighting_Management_Standalone_Presence_Sensor_Ceilin
g.rfa | RFA (3.23Mo)