

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - PIR 270° lighting sensor 18m - IP55 - surface wall or ceiling mounting

REF. 048933 | EAN KODA. 3245060489335

> [The product details page](#)

Značilnosti izdelka:

- PIR detection 270°, range 18m at 2,5m high
- IP55
- Switching control (3 - wire with neutral)
- Multi lens sensor with directional head, range 18 m
- Standby consumption: 0.7 W

Prednosti montaže:

- Precise on-site adjustment using configuration tool Cat.No 0 882 40Can be mounted on an angle using accessory Cat.No 0 489 72

Prednosti uporabe:

- Ideal for outdoor and humid areas with natural light

Edinstvene značilnosti:

- Can be used with push-button Cat.No 0 770 40 for vacancy mode (manual switch-on and manual or automatic switch-off)

Dokumentacija

Tehnična dokumentacija

-  LE07602AA.pdf | PDF (9.21Mo)
-  S000081482EN_2.pdf | PDF (3.53Mo)
-  LE06324AB.pdf | PDF (1.69Mo)
-  S000081482FR_2.pdf | PDF (3.51Mo)

CAD & specifikacije načrtov / BIM

Legrand_Lighting_Management_Standalone_Presence_Sensor_Wall.rfa | RFA (0.93Mo)

Legrand_Gestion_eclairage_Detecteur_Presence_Mur_autonome.rfa | RFA (0.93Mo)

Katalog & drugo

-  ex223001_0891.pdf | PDF (0.05Mo)
-  ex223001_0888.pdf | PDF (0.07Mo)

Pogodbe in certifikati

-  LGRP-01574-V01.01-EN.pdf | PDF (0.64Mo)