

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - PIR 360° motion sensor Ø8m - IP20 - surface ceiling mounting

REF. 048948 | EAN KODA. 3414970809483

> [The product details page](#)

Značilnosti izdelka:

- PIR detection 360°, range Ø8m at 2.5m height
- IP20
- Switching control (3 - wire with neutral)
- Standby consumption: 0.75 W
- Cardboard

Priporočila / omejitve

- Voltage 230VAC 50/60Hz only Optimum distance between 2 sensors: 6 m

Prednosti montaže:

- Installed directly on surface ceiling

Prednosti uporabe:

- Ideal for passage areas without natural light

Edinstvene značilnosti:

- Cost effective solution
- Automatic switch-on taking into account the ambient light level
- Easy basic settings through a simple screw driver

Dokumentacija

Tehnična dokumentacija

-  S000087115FR-4.pdf | PDF (1.69Mo)
-  LE09144AB.pdf | PDF (1.08Mo)
-  S000087115EN-2.pdf | PDF (0.97Mo)

CAD & specifikacije načrtov / BIM

Legrand_Gestion_eclairage_Detecteur_mouvement_Plafond_autonomie.rfa | RFA (0.66Mo)

Legrand_Lighting_Management_Standalone_Motion_Sensor_Ceiling.rfa | RFA (0.66Mo)

Katalog & drugo

 ex223001_0885.pdf | PDF (0.07Mo)

Pogodbe in certifikati

-  LGRP-00140-V01.01-EN.pdf | PDF (0.56Mo)
-  LGRP-00154-V02.01-FR.pdf | PDF (0.77Mo)
-  OC / CB-685326 | (0.52Mo)
-  LGRP-00154-V02.01-EN.pdf | PDF (0.81Mo)