

Naziv PDF datoteke



LEGRAND

Sounder - IP21 - IK07 - 90 dB - 12/24/48 V= - white

REF. 040586 | EAN KODA. 3245060405861

> [The product details page](#)

Značilnosti izdelka:

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounders - Conform to EN 54 - 3 standard and CE CPR approved - IP 21 - IK 07 - Flush-mounting in false ceiling - Sound level : 90 dB at 2 meters - NF S 32 - 001 sound - Voltage range : 10 - 58 V - Average consumption : 12 V DC 5 mA - 24 V DC 9 mA - 48 V DC 13 mA

Dokumentacija

Tehnična dokumentacija



LE02620AC.pdf | PDF (2.63Mo)

Pogodbe in certifikati



NFSSI Composant-DS 033 A2 | (0.26Mo)



LGRP-00272-V01.01-FR.pdf | PDF (0.61Mo)

Katalog & drugo



ex223001_0921.pdf | PDF (0.05Mo)