

# Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - Electronic room thermostat - 2 modules - white

REF. 076720 | EAN KODA. 4010957767204

[> The product details page](#)

## Značilnosti izdelka:

- Mosaic™ Programme mechanisms - heating, temperature regulation
- Room thermostats - Power supply 230 V~ - 50/60 Hz - Suitable for regulation of ceiling panel heating and direct floor heating Electronic - Adjustment range from 5 °C to 30 °C - Adjustment accuracy +/- 0,5 °C (category B) - One output by non-powered contact - Pushbutton on Front face for selecting the operating mode (off, switch off when temperature falls or rises) - LV use - Breaking capacity : - 8 A / 230 V~ - resistive circuit - 2 A / 230 V~ - inductive circuit - ELV use - Breaking capacity from 1 mA min. to 500 mA max. 12 to 48 V~ / 12 to 24 V - White

## Dokumentacija

### Tehnična dokumentacija

-  F01857EN-01.pdf | PDF (0.24Mo)
-  F01857FR-01.pdf | PDF (0.24Mo)
-  292249-05.pdf | PDF (1.3Mo)

### CAD & specifikacije načrtov / BIM

- BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)
- BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

### Katalog & drugo

-  ex223001\_1180.pdf | PDF (0.08Mo)