

Naziv PDF datoteke



NILOÉ™ LEGRAND

Niloé™ - Thermostat 230 V - White

REF. 764587 | EAN KODA. 3414970683038

> [The product details page](#)

Značilnosti izdelka:

- Nilo - shutter controls, keycard switches and thermostats - Mechanisms supplied with cover plates and support frames in flow - pack - To be equipped with plates - Screw terminals - Fixing with screws or claws (supplied)
- Electronic room thermostat - For direct radiant ceiling panels and underfloor heating - Adjustment range : from 10 °C to 30 °C - Frost protection 7 °C - Adjustment precision : 0,5 °C - 1 potential free N/O contact - Switching capacity : - 8 A - 250 V~ - resistive circuit - 2 A - 250 V~ - inductive circuit - Power supply : 230 V~ 50/60 Hz - Adjustable b Rightness of LEDs - Can be associated with a clock for comfort and eco mode - White

Dokumentacija

Tehnična dokumentacija

-  F02163FR-00.pdf | PDF (1.04Mo)
-  LE09397AA.pdf | PDF (0.54Mo)
-  F02163EN-00.pdf | PDF (0.53Mo)

Katalog & drugo

-  ex223001_0744.pdf | PDF (0.14Mo)