

Naziv PDF datoteke



LEGRAND

Sounder beacons - IP65 - IK07 - 90 dB - 12/24/48 V= - red

REF. 040591 | EAN KODA. 3245060405915

> [The product details page](#)

Značilnosti izdelka:

- Sounders, sounder beacons, bells, electromagnetic door holder and safety electrical power supplies
- Sounder beacons - Conform to EN 54 - 3 standard and CE CPR approved - Sound level : 90 dB at 2 meters - NF S 32 - 001 sound - Red flash - Voltage range : 10 - 58 V - Average consumption : 12 V DC 23 mA ; 24 V DC 22 mA ; 48 V DC 23 mA - IP 65 - IK 07 - Surface - mounting - 2 cable glands supplied

Dokumentacija

Tehnična dokumentacija



LE02619AB.pdf | PDF (1.32Mo)

Pogodbe in certifikati



LGRP-00277-V01.01-EN.pdf | PDF (0.57Mo)

Katalog & drugo



ex223001_0921.pdf | PDF (0.05Mo)