

Naziv PDF datoteke



SYNERGY™ LEGRAND

Synergy™ Authentic - 2 gang unswitched US standard socket outlet 15A - Brushed Stainless Steel

REF. 833299 | EAN KODA. 3414970760265

> [The product details page](#)

Značilnosti izdelka:

- US standard 15A 127V~
- 2X2P+E Type B socket
- Cover plate is square 86x146 mm, product thickness is 7mm (once is installed onto the wall).
- Monobloc complete product = ready-to-install product

Priporočila / omejitve

- Recommended inside use only

Prednosti montaže:

- Strip length indicator avoids waste of wires. Terminal screws backed off ready to cabling

Edinstvene značilnosti:

- Plate in austenitic stainless steel Non magnetic Grade 304L
- Made in UK
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Dokumentacija

Katalog & drugo



ex223001_0725.pdf | PDF (0.08Mo)