

Naziv PDF datoteke



DLPLUS LEGRAND

DLPlus Mini-Trunking 2 compartments with a central separation partition, 20x12,5mm. White

REF. 030007 | EAN KODA. 3245060300074

> [The product details page](#)

Značilnosti izdelka:

- Delivered in 60 units of length 2,10m
- Comply with reliability, safety and technical performance requirements accord EN50085 - 2 - 1
- IP40 : protected against solid bodies larger 1mm maximum. Shock resistance at 2 joules.

Prednosti montaže:

- Fixing by: gluing (Neoprene glue (cat.no 030949), wall plug (cat.no 030898, 030899), DLP rapid wall plug (ref 0308 97) or screw, nails...

Prednosti uporabe:

- Can be installed in tertiary and residential

Dokumentacija

Tehnična dokumentacija

 F00988EN-06.pdf | PDF (2.71Mo)

 F00988FR-04.pdf | PDF (2.59Mo)

Pogodbe in certifikati

 NF Conduits-NF 593021O | (0.08Mo)

 LGRP-01603-V02.01-EN.pdf | PDF (0.92Mo)

 LGRP-01603-V02.01-FR.pdf | PDF (0.88Mo)

Katalog & drugo

 ex223001_1044.pdf | PDF (0.13Mo)

 ex223001_1048.pdf | PDF (0.04Mo)