

Naziv PDF datoteke



TX³ LEGRAND

MCB TX3 6000A 3 pole 16A curve B

REF. 403402 | EAN KODA. 3414970387547

[> The product details page](#)

Značilnosti izdelka:

- Breaking capacity 6000A according to IEC 60898 - 1 standard for household installations. Tripping threshold in case of short - circuit between 48A and 80A (B curve between 3 In and 5 In)
- Can be supplied either by copper cable, prong busbar (top side or bottom side) or fork busbar (bottom side).
- Protected against solid bodies larger than 12,5mm ("fingerproof") : IP20 according to IEC/EN 60529 standard. Maximum level of limitation of the let through energy (energy limitation class 3 according to IEC 60898 - 1 standard).
- Can be equipped with Legrand DX3 auxiliaries and accessories. Can be connected to aluminium cable with Legrand DX3 terminal accessory n° 4 063 10.
- This device complies with substance-restriction requirements and has been designed in an environmentally conscious process.

Priporočila / omejitve

- This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Prednosti montaže:

- Fitted with a special DIN rail clamp, bottom side, allowing an independent removal of this product when the fork busbar supplying the row is still in place.

Prednosti uporabe:

- Fitted with a label holder allowing a clear, visible and convenient identification of the circuit. On and OFF indication printed on the handle respectively on red and green backgrounds for an easy identification of the status of the MCB.

Dokumentacija


Tehnična dokumentacija

 F01547EN-01.pdf | PDF (2.97Mo)


CAD & specifikacije načrtov / BIM

 403551.dwg | DWG (0.27Mo)

Katalog & drugo

 ex223001_0056.pdf | PDF (0.12Mo)

Pogodbe in certifikati

 VDE-40042432 | (0.69Mo)

 LGRP-00763-V02.01-EN.pdf | PDF (0.78Mo)

 OC / CB-IT-15813 | (0.15Mo)