

Naziv PDF datoteke



LEGRAND

Dimmer - for incadescent/halogen lamp 230 V~ - load 60 to 600 W- 2 modules

REF. 003659 | EAN KODA. 3245060036591

> [The product details page](#)

Značilnosti izdelka:

- Lighting management remote control dimmers
- Remote control dimmers 100 - 240 V~ - 50/60 Hz - Symmetrical rail mounting - The last lighting level is stored into memory, In phase of power cut or switch - off - Direct or remote control (switching and dimming) with non-illuminated push - buttons For incandescent and halogen lamps - Suitable for incandescent and halogen lamps 230 V~, ELV halogen lamps with ferromagnetic transformers - Load : 60 to 600 W (for 230 V~ 50/60 Hz) - Number of modules : 2

Dokumentacija

Tehnična dokumentacija



0064GS3-00.pdf | PDF (0.2Mo)

Katalog & drugo



ex223001_0108.pdf | PDF (0.08Mo)