

Naziv PDF datoteke



LEGRAND

Remote control dimmer via BUS line - fluorescent lamp with 0-10V ballast - max 1000 VA - DIN 4 modules

REF. 003660 | EAN KODA. 3245060036607

> [The product details page](#)

Značilnosti izdelka:

- For fluorescent lamps with 1 - 10V ballast (fluorescent tubes and compact fluorescent lamps with separated ballast)
- Ballast power : maximum 1000VA
- Mains voltage 100/240VAC - 50/60Hz
- DIN 4 modules
- Control current: 50 mA

Prednosti montaže:

- Symmetrical rail mounting

Prednosti uporabe:

- Equipped with illuminated scale indicating the light level of controlled lamps

Edinstvene značilnosti:

- Equipped with illuminated scale indicating the light level of controlled lamps

Dokumentacija

Tehnična dokumentacija



0064JR4-03_FR.pdf | PDF (0.52Mo)



0064JR4-03_EN.pdf | PDF (0.52Mo)

CAD & specifikacije načrtov / BIM



003660.dwg | DWG (0.1Mo)

Katalog & drugo



ex223001_0108.pdf | PDF (0.08Mo)