

Naziv PDF datoteke



MOSAIC™ LEGRAND

Mosaic™ - Dimmer switch - 0-10 V - for electronic ballasts - 2 modules - white

REF. 078404 | EAN KODA. 3245060784041

> [The product details page](#)

Značilnosti izdelka:

- Mosaic™ Programme mechanisms - dimming control
- Dimmer switch with neutral, for 1 - 10 V ballast - For lamps with 1 - 10 V ballast, 600 VA - White

Dokumentacija

Tehnična dokumentacija

 F00751FR-00.pdf | PDF (0.45Mo)

 0064JX2-03.pdf | PDF (0.78Mo)

CAD & specifikacije načrtov / BIM

BIM-LEGRAND-MOSAIC-2025-FRANCAIS.rvt | RVT (124.38Mo)

BIM-LEGRAND-MOSAIC-2025-ENGLISH.rvt | RVT (125.73Mo)

Katalog & drugo

 ex223001_1177.pdf | PDF (0.07Mo)

Pogodbe in certifikati

 OC / CB-630164B/A1 | (0.56Mo)

 NF App Domestic-NF012_1945 | (0.74Mo)