

Naziv PDF datoteke



NILOÉ™ LEGRAND

Niloé™ - Rotary dimmer - 300 W- 2-wire - Ivory

REF. 764688 | EAN KODA. 3414970684721

> [The product details page](#)

Značilnosti izdelka:

- Nilo - automatic switches and dimmers - Mechanisms supplied with cover plates and support frames in flow - pack - To be equipped with plates - Screw terminals - Fixing with screws or claws (supplied)
- Rotary dimmers 300 W - 2 - wire - Equipped with overvoltage and short - circuit protection - When switched on, gradually (2 seconds) light up at the level set before last switch - off - Can be remotely controlled via non-illuminated pushbuttons, with each push - button able to perform the ON/OFF and dimming function - Screw terminals - For all types of lamps : - dimmable LEDs : 5 W to 75 W (10 lamps max.) - halogen with ferromagnetic or electronic transformer : 5 VA to 300 VA - fluorescent tube - ballast : 5 VA to 300 VA - halogen and incandescent 240 V~ : 5 W to 300 W - Ivory

Dokumentacija

Tehnična dokumentacija



F02164FR-00.pdf | PDF (1.04Mo)



LE08859AA_1.pdf | PDF (1.05Mo)



F02164EN-00.pdf | PDF (1.04Mo)

Katalog & drugo



ex223001_0744.pdf | PDF (0.14Mo)