

Naziv PDF datoteke



DLP LEGRAND

Mosaic support 6 modules for 65mm cover

REF. 010956 | EAN KODA. 3245060109561

> [The product details page](#)

Značilnosti izdelka:

- Plate : width 67,5mm, length 194,4mm
- Support : width 64,5mm, length 210,4mm
- Colour : grey support, white finishing plate

Prednosti montaže:

- Enclippable and juxtaposable support, delivered with a finishing plate

Prednosti uporabe:

- Allows the assembly of Mosaic sockets 6 standard modules French in horizontal position

Dokumentacija

Tehnična dokumentacija

 F00885FR-05.pdf | PDF (1.98Mo)

 F00885EN-06.pdf | PDF (2.22Mo)

CAD & specifikacije načrtov / BIM

BIM-LEGRAND-GOULOTTES-BELGIQUE-2024.rvt | RVT (23.93Mo)

BIM-LEGRAND-TRUNKING-EXPORT-2024.rvt | RVT (14.36Mo)

BIM-LEGRAND-GOULOTTES-FRANCE-2024.rvt | RVT (13.17Mo)

Katalog & drugo

 ex223001_1077.pdf | PDF (0.14Mo)

Pogodbe in certifikati

 LGRP-01605-V02.01-EN.pdf | PDF (0.75Mo)

 OC / CB-FR_705591/A3 | (0.73Mo)

 OC / CB-FR_707308/A3 | (4.23Mo)

 MEEI-UP 69265956 002 | (1.87Mo)

 NF Conduits-601796A | (0.42Mo)

 NF App Domestic-NF012_2201/A2 | (1.3Mo)

 LGRP-01605-V02.01-FR.pdf | PDF (0.71Mo)

 LGRP-01223-V02.01-FR.pdf | PDF (0.83Mo)