

Naziv PDF datoteke



SYNERGY™ LEGRAND

Synergy™ Sleek - 2gang double pole switch 45A + BS 13A switched socket outlet cooker marking - Glossy Gold

REF. 832429 | EAN KODA. 3414970663009

> [The product details page](#)

Značilnosti izdelka:

- 45A 250V 13A 250V~
- Screw terminals accept wires up to 16mm²
- For BS type 47 mm 2 gangs flush mounting boxes
- Screwless cover plate is square 86x146 mm, product thickness is 4mm (once is installed onto the wall).
- Complete product, cover plates are clipped onto the mechanism itself.

Priporočila / omejitve

- Recommended inside use only

Prednosti montaže:

- Compact mechanisms for maximum wiring space and slim front plates

Prednosti uporabe:

- Complies to British Standards certifications for heavy loads. Fitted with safety shutters to maximise child protection

Edinstvene značilnosti:

- Plate and rockers are made in the same Stainless Steel - Grade 430, with a chromium plating which bring a better rusting resistance and a nicer finish
- Oblong blue led power indicator which size is 11mm x 1,5mm, LED technology ensures the maximum quality in terms of reliability, efficiency, maintenance and energy saving
- Delivered with screws for flush & surface boxes in both plastic and metal boxes

Dokumentacija

Tehnična dokumentacija

 F02365EN-00.pdf | PDF (0.1Mo)

Pogodbe in certifikati

 G-MARK-0032-1874-V-1 | (15.29Mo)

 OC / CB-FR_707920 | (0.58Mo)

 OC / CB-FR_719319 | (0.72Mo)

 OC / CB-FR_719316 | (0.77Mo)

Katalog & drugo

 ex223001_0730.pdf | PDF (0.09Mo)

