

Naziv PDF datoteke



LEGRAND

Bulkhead light - IP44 - IK06 - oval 60 W- E27 - metal grid screw fixing -grey

REF. 060415 | EAN KODA. 3245060604158

> [The product details page](#)

Značilnosti izdelka:

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- Oval - IP 44 / IK 06 - Polypropylene base - Glass diffuser - Galvanised steel or plastic - Protection wire grid - 3 side knockable entries, for 16, 20 mm - cable - 230 V - 50 Hz - Self - extinguishing : 850 °C - For compact fluorescent lamps - Porcelain lampholder - Screw terminals 12 W - E 27 - Grey - Metal grid - screw Fixing

Dokumentacija

Tehnična dokumentacija



LE12201AA.pdf | PDF (0.46Mo)

Pogodbe in certifikati



LGRP-00121-V01.01-EN.pdf | PDF (0.57Mo)

Katalog & drugo



ex223001_0901.pdf | PDF (0.09Mo)



ex223001_0902.pdf | PDF (0.09Mo)