

Naziv PDF datoteke



LEGRAND

Bulkhead light - IP55 - IK04 - round - 100 W- E27 - tough environments

REF. 060483 | EAN KODA. 3245060604837

> [The product details page](#)

Značilnosti izdelka:

- IP 44/54/55 weatherproof bulkhead lights - For domestic, commercial areas and tough environments
- IP 55 - IK 04 bulkhead lights for tough environments IP 55 - IK 04 bulkhead lights - Metal/glass bulkhead lights. - For exterior/indoor use - For industrial use. Earth terminal - 3 entries in T. Operating temperature : - min. : - 30 °C - max. : + 35 °C - Can be equipped with metal protection grid for IK 07 protection - E 27 - Round - for 70 W halogen, 20 W compact fluorescent or 12 W LED lamps - With colourless diffuser

Dokumentacija

Tehnična dokumentacija

 F00324FR-00.pdf | PDF (0.31Mo)

 LE11377AA.pdf | PDF (0.14Mo)

Pogodbe in certifikati

 LGRP-00520-V01.01-EN.pdf | PDF (0.57Mo)

Katalog & drugo

 ex223001_0901.pdf | PDF (0.09Mo)

 ex223001_0902.pdf | PDF (0.09Mo)