

# Naziv PDF datoteke



LCS<sup>3</sup> LEGRAND

Gigabit managed ethernet PoE switch with 10 RJ45 ports and 2 SFP .

REF. 033490 | EAN KODA. 3414971717060

This gigabit managed switch is an active device that connects devices together on a network. It supplies power until 130W and data to any ethernet-enabled device such as wifi access point, voIP phones, security cameras, IT gateways.

> [The product details page](#)

## Splošni opis:

This gigabit managed switch is an active device that connects devices together on a network. It supplies power until 130W and data to any ethernet-enabled device such as wifi access point, voIP phones, security cameras, IT gateways.

### Značilnosti izdelka:

- Managed
- 8 RJ45 Gigabit 802.3af/at PoE+ ports, 2 Gigabit ethernet uplink ports and 2 shared Gigabit SFP uplink ports
- 130 Watt PoE power budget
- 20Gbps switching capacity
- Layer 3 switching, static routing. 802.1Q VLAN (with trunking) and Quality of Service support.

### Priporočila / omejitve

- Can supply up to 25.5W per port or 130W combined consumption of all external POE devices.

## Dokumentacija

### Tehnična dokumentacija

-  S000106533EN-00.pdf | PDF (0.07Mo)
-  LE11421AA-XMS1208P.pdf | PDF (0.26Mo)
-  GuideAnglais-XMS1208P.pdf | PDF (1.13Mo)
-  Guide-XMS1208P.pdf | PDF (1.49Mo)
-  S000106533FR-00.pdf | PDF (0.56Mo)

### Prednosti montaže:

- Plug & play and easy to install. Included rack-mount kit to install in a 19 inches unit, and rubber feet to use as a desktop device. Power cord with 2P+E French/German plug supplied.

### Prednosti uporabe:

- Fanless for silent operations. Simple power management of PoE-enabled devices.

### Katalog & drugo

-  ex223001\_0995.pdf | PDF (0.09Mo)